

# BF & BD series

Proportional single axis paddle joystick controllers •  
non-contacting Hall effect technology



## DISTINCTIVE FEATURES

- Sprung or detent options
- Sprung to center or south options
- Two lever heights available
- Inserts available in black, red, blue, yellow & green
- Analog or PWM outputs
- Zero below panel depth



## ENVIRONMENTAL SPECIFICATIONS

- Operating Temperature: -25 °C to +70 °C (-13 °F to +158 °F)
- Storage Temperature: -40 °C to +70 °C (-40 °F to +158 °F)
- Above Panel Sealing: IP67
- EMC Immunity Level: EN61000-4-3 (extended) 100 V/m
- EMC Emissions Level: EN61000-6-3:2001, CISPR 22: 2005 Class B 30MHz – 11GHz
- ESD: EN61000-4-2 (extended)



## ELECTRICAL SPECIFICATIONS

- Supply Voltage Range: 5 V  $\pm$  0.5 V
- Reverse Polarity Max: -10 V
- Overvoltage Max: +20 V
- Recommended min load: 10  $\Omega$
- Return to Center Voltage Tolerance:  $V/2 \pm (5\% \times \text{Gain})$



## MECHANICAL SPECIFICATIONS

- Maximum Vertical Load: IK08 (BSEN62262:2002)
- Maximum Horizontal Load: 75 N (16.86 lbf)
- Mechanical Angle of Movement: 50°
- Expected Mechanical Life: 5 million (sprung to center versions); 2 million (detent and sprung to south versions) lifecycles
- Mass/weight: 50 g (1.76 oz.)
- Lever Action (centering): Sprung and friction

The company reserves the right to change specifications without notice.



# BF & BD series

Proportional single axis paddle joystick controllers  
non-contacting Hall effect technology




## MATERIALS

- Housing: Polyetherimide, polycarbonate
- Handles: Polyetherimide, polycarbonate



## MOUNTING

### PANEL CUT-OUT - DROP-IN MOUNTING



The Paddle may be mounted with two different hole patterns:

- Two screws – in line on the Y axis (shown as yellow screws)
- Four screws – one in each corner (shown as silver screws)

The Paddle is fitted with M3 bushes in all six positions, as standard.

Fasteners are not supplied as standard. The appropriate length of fastener is dependent on panel thickness.

When mounting the Paddle, care should be taken to site it in a position that does not make it vulnerable to damage when in use. If the Paddle is intended for use in a handheld enclosure then care must be taken to protect the Paddle from damage caused by dropping. Basic precautions such as mounting it at the lightest end of the enclosure so it doesn't hit the ground first or by protecting it with a guard should always be implemented for long term reliability.


The body of the Paddle, on the underside of the panel, must not be subject to water spray, excessive humidity or dust.



## CONNECTIONS

Paddles are supplied with an eight way connector as standard.

PIN	FUNCTION
1	5V
2	Blank
3	0V
4	Analog/PWM output 1
5	Analog/PWM output 2
6	0V
7	Blank
8	5V



**OMEGA FUSIBILI**  
Via Edison, 10  
I-20057 Assago (MI)  
ITALIA  
omega@omegafusibili.it  
Tel.: (+39)02488481

**OMEGA COMPOSANTS**  
220 rue Ferdinand Perrier  
69800 Saint-Priest  
FRANCE  
omega@omegacomposants.fr  
Tel.: +33(0)478908564

**ERMEC PORTUGAL**  
Rua Brito Capelo, 807  
P-4450-068 Matosinhos  
PORTUGAL  
portugal@ermec.com  
Tel.: (+35)1707509539

**ERMEC SPAIN**  
Avda. Arraona, 85 Nave 4  
E-08210 BARBERA DEL VALLES  
SPAIN  
comercial@ermec.com  
Tel.: (+34)934501600







## LEVER OPERATION

### DETENT OPTIONS


D01 = CENTER DETENT




D02 = +/-12.5 DEGREES



D03 = +/- 12.5 & 25 DEGREES




D04 = +/-25 DEGREES




### SPRUNG TO CENTER WITH DETENT OPTIONS


SD1 = CENTER DETENT




SD2 = +/-12.5 DEGREES




SD3 = +/- 12.5 & 25 DEGREES




SD4 = +/- 25 DEGREES



A01 (Sprung to centre)



A02 (Sprung to south)



**OMEGA FUSIBILI**  
Via Edison, 10  
I-20057 Assago (MI)  
ITALIA  
omega@omegafusibili.it  
Tel.: (+39)02488481

**OMEGA COMPOSANTS**  
220 rue Ferdinand Perrier  
69800 Saint-Priest  
FRANCE  
omega@omegacomposants.fr  
Tel.: +33(0)478908564

**ERMEC PORTUGAL**  
Rua Brito Capelo, 807  
P-4450-068 Matosinhos  
PORTUGAL  
portugal@ermec.com  
Tel.: (+35)1707509539

**ERMEC SPAIN**  
Avda. Arraona, 85 Nave 4  
E-08210 BARBERA DEL VALLES  
SPAIN  
comercial@ermec.com  
Tel.: (+34)934501600



# BF & BD series

Proportional single axis paddle joystick controllers •  
non-contacting Hall effect technology



## BUILD YOUR PART NUMBER

### PADDLE

<b>BF</b>	74 mm (2.91 in) above the panel
<b>BD</b>	50 mm (1.97 in) above the panel

### CONFIGURATION

<b>1</b>	Standard Dual Outputs
<b>2</b>	Inverse Dual Outputs
<b>3</b>	PWM

### GAIN

<b>10</b>	±10%xV
<b>25</b>	±25%xV
<b>30</b>	±30%xV
<b>40</b>	±40%xV
<b>50</b>	±50%xV

### LEVER OPERATION

<b>A01</b>	Sprung to Center
<b>A02</b>	Sprung to South
<b>D01</b>	Center Detent
<b>D02</b>	12.5 Degree Detents
<b>D03</b>	12.5 & 25 Degree Detents
<b>D04</b>	25 Degree Detents
<b>SD1</b>	Sprung to Center with D1
<b>SD2</b>	Sprung to Center with D2
<b>SD3</b>	Sprung to Center with D3
<b>SD4</b>	Sprung to Center with D4

### INSERT COLOR

<b>BK</b>	Black
<b>RE</b>	Red
<b>BL</b>	Blue
<b>YE</b>	Yellow
<b>GR</b>	Green

**00** No Switches

### MODIFIER

**00** None

**ERMEC,SL BARCELONA**  
Avda.Arraona,85, Nave 4  
08210 Barberà del Vallès  
España  
bcn@ermec.com  
Tel.: (+34)93.450.16.00

**ERMEC MADRID**  
c/Puerto Rico, 4  
28222 Majadahonda  
España  
madrid@ermec.com  
Tel.: (+34)91.828.56.51

**ERMEC PORTUGAL**  
Rua Brito Capelo, 807  
4450-068 Matosinhos  
Portugal  
portugal@ermec.com  
Tel.: (+35)1707509539

**ERMEC BILBAO**  
bilbao@ermec.com  
Tel.: (+34)91.828.56.51


www.ermec.com




# BF & BD series

Proportional single axis paddle joystick controllers •  
non-contacting Hall effect technology

## BF PADDLE




## BD PADDLE




## VOLTAGE OUTPUT OPTIONS

### DUAL OUTPUT - CONFIGURATION 1



### DUAL OUTPUT - CONFIGURATION 2



— Output 1  
- - - Output 2



# BF & BD series

Proportional single axis paddle joystick controllers •  
non-contacting Hall effect technology



## CONFIGURATION OPTIONS

### OUTPUT OPTIONS

The BF & BD series Paddle is configured as two "electrical" controls in one mechanical package. The Paddle operates from 5V and provides two proportional outputs. The second output is accurate to the first within  $\pm 3\%$  of the power supply. The power supply for the secondary output is also completely independent. Customers may choose their preference of voltage outputs (gains).

The secondary output can be of the same or inverse polarity to the primary wiper. For example, with a secondary inverse output, the first and second outputs can be summed and compared to zero to verify that the joystick is operating correctly. Paddles having two identical outputs of the same polarity may be used to drive two identical dual redundant circuits.

The BF series Paddle may be specified with a variety of PWM output options. For more details on available PWM options please refer to APEM.

### POWER SUPPLY

The BF & BD Series is designed to be powered by a regulated  $5V \pm 0.5V$  power supply. The outputs are ratiometric, making a stable, noise free, power supply essential. The power supply to the joystick should be carefully regulated to be within tolerance.

Should the power supply change outside of the specified tolerances, permanent damage may occur.

### MAGNETIC IMMUNITY AND SYSTEM DESIGN

The BF & BD Series incorporates internal magnetic screening to minimize the effect of external magnetic fields. Mounting or operating the Paddle close to strong magnetic fields is not recommended. System designers should follow best practice when incorporating the BF Series Paddle into their products.

Care should be taken to decouple the power supply properly and to employ adequate EMC shielding.

### HANDLE OPTIONS

The BF & BD series offers two standard handle options. The taller (74mm) handle provides the most ergonomic solution while the shorter (50mm) is best suited to hand held applications where a minimized height is preferred. The taller lever is supplied with the top insert prefitted, however the shorter lever may be specified with no insert fitted and the snap in inserts supplied loose for ease of customer integration.

Note: All snap in inserts may only be fitted once, and are not removable once fitted.

### SELECTABLE SWITCHING POINTS

The Paddle incorporates two Hall effect switches. The angle of the lever at the switch trigger point can be selected when ordering.

If no switches are specified then the output on pins 2 and 7 will be unused.

The outputs are configured as 'open drain' type with a 1K5 pull up resistor to 5V.

### GAIN OPTIONS

The voltage output on the wiper, at full scale deflection is determined by the gain. The gain is expressed as a percentage of the voltage supplied.

Therefore (assuming a 5V supply) a Paddle specified with  $\pm 25\%$  gain would yield 1.25V at South, 2.5V at center and 3.75V at North. A range of gain options are available as standard.

All controls are supplied pre-set and no further calibration is needed throughout the lifetime of operation.

### OUTPUT IMPEDANCE

The voltage outputs at center and at each end of travel are specified across an infinite load, with no current flowing. The output impedance specified in the electrical specification should be taken into account when designing a system.

Load resistance of less than 10K Ohms is not recommended.

**ERMEC, SL BARCELONA**  
Avda. Arraona, 85, Nave 4  
08210 Barberà del Vallès  
España  
bcn@ermec.com  
Tel.: (+34)93.450.16.00

**ERMEC MADRID**  
c/Puerto Rico, 4  
28222 Majadahonda  
España  
madrid@ermec.com  
Tel.: (+34)91.828.56.51

**ERMEC PORTUGAL**  
Rua Brito Capelo, 807  
4450-068 Matosinhos  
Portugal  
portugal@ermec.com  
Tel.: (+35)1707509539

**ERMEC BILBAO**  
bilbao@ermec.com  
Tel.: (+34)91.828.56.51

www.ermec.com

